

Philips  
Professional LCD TV

32"

LCD Pro:Idiom™ with MPEG-4

32HFL5860L



## Lodgenet HD Built-In Hospitality TV

### MPEG-4 and Pro:Idiom™ Plus

The perfect plug and play PPV television optimized for Lodgenet installations, this set allows easier setup without room visit hassles or charges. In addition, this set offers Philips unique SmartPower<sup>2</sup> and Five Star Service.

#### Designed for hotel use

- Lodgenet® HD Built-in
- HD content protection with Pro:Idiom™ Plus
- VTrack™ forensic watermark
- MPEG-4 for the latest HD signals
- SmartStand

#### Best total cost of ownership

- Five Star Service - two-year advanced exchange warranty
- SmartPower<sup>2</sup> and ESP for energy savings
- On-shore 24/7 help desk

#### Sustainable and safe

- Lead-free/RoHS compliant with flame retardant housing

#### Differentiating guest experience

- USB media autoplay
- SmartWindow for simultaneous TV viewing and PC use

**PHILIPS**  
sense and simplicity

## Specifications

### Picture/Display

- **Aspect ratio:** 16:9, Widescreen
- **Brightness:** 500 cd/m<sup>2</sup>
- **Contrast ratio (typical):** 1200:1
- **Dynamic screen contrast:** 9600:1
- **Diagonal screen size:** 32 inch / 80 cm
- **Picture enhancement:** Pixel Plus 3 HD, Progressive Scan, 3/2 - 2/2 motion pull down, Active Control, 3D Combfilter, Dynamic contrast enhancement, Contrast Plus, Digital Noise Reduction, Jagged Line Suppression, Luminance Transient Improver, Color Transient Improvement, Automatic skin tone correction, Color Enhancement, Motion adaptive de-interlacing, Picture in Picture
- **Screen enhancement:** Anti-Reflection coated screen
- **Display screen type:** LCD WXGA Active Matrix TFT
- **Panel resolution:** 1366 x 768p
- **Response time (typical):** 8 ms
- **Viewing angle (H / V):** 178 / 178 degree

### Supported Display Resolution

#### • Computer formats

Resolution	Refresh rate
640 x 480	60Hz
800 x 600	60Hz
1024 x 768	60Hz
1366 x 768	60Hz

#### • Video formats

Resolution	Refresh rate
480i	60Hz
480p	60Hz
720p	60Hz
1080i	60Hz
1080p	24Hz, 25Hz, 30 Hz
1080p	50Hz, 60Hz

### Sound

- **Sound System:** Stereo, Dolby Digital (AC-3)
- **Output power (RMS):** 2 x 10W
- **Sound Enhancement:** Auto Volume Leveller, Incredible Surround

### Loudspeakers

- **Built-in speakers:** 2

### Convenience

- **Ease of Installation:** Fine Tuning, PLL Digital Tuning, Program Name, Advanced Hotel Mode, Cloning of TV settings via USB, Keyboard lock-out, Security menu access
- **Ease of Use:** Auto Volume Leveller (AVL), Smart Picture Control, Smart Sound Control
- **Screen Format Adjustments:** 4:3, 7 Widescreen Modes
- **Comfort:** Hotel Guest features, Sleep timer, Switch on channel, Volume limitation, Welcome message

- **Other convenience:** Kensington lock
- **Convenience Enhancements:** Closed captioning (digital), Vchip and parental lock
- **Interactive hotel features:** Smoovie Pay TV

### Tuner/Reception/Transmission

- **Tuner bands:** Hyperband, S-Channel, UHF, VHF
- **TV system:** ATSC, NTSC
- **Video Playback:** NTSC, PAL
- **Number of Preset Channels:** 250
- **Cable:** Unscrambled Digital Cable -QAM
- **Terrestrial:** ATSC (8VSB)
- **Aerial Input:** 75 ohm F-type

### Connectivity

- **AV 1:** AV In, S-Video Y/C
- **AV 2:** Audio L/R in, YPbPr
- **AV 3:** VGA PC-in, Audio-in mini jack 3.5mm
- **Connectivity Enhancements:** SmartCard Expansion Slot, HM-Link, Extra Power supply 12V/1W, External Loudspeaker connector, USB2.0, RJ12 SmartPlug connector
- **Audio Output - Digital:** Coaxial (cinch)
- **Other connections:** Antenna F-type, RS232 Serial
- **AV 4:** HDMI
- **AV 5:** HDMI

### Power

- **Power consumption:** 150 W
- **Mains power:** 110 - 240V, 50/60Hz
- **Ambient temperature:** 5 °C to 40 °C
- **Standby power consumption:** 1.16

### Dimensions

- **Color cabinet:** Black w/gloss black bezel
- **Set dimensions in inch (W x H x D):** 31.7 x 21.5 x 4.4 inch
- **Set dimensions with stand in inch (W x H x D):** 31.7 x 24 x 10.4 inch
- **Box dimensions in inch (W x H x D):** 34.2 x 24.8 x 13.6 inch
- **Product weight (lb):** 34.1
- **Weight incl. Packaging (lb):** 44.5
- **VESA wall mount compatible:** 200 x 100 mm

### Accessories

- **Included Accessories:** Power cord, Warranty Leaflet, Swivel stand with anti-theft, Quick start guide
- **Optional accessories:** Set up Remote RC2573GR, Mounting brackets/ stands, Guest remote control

### Multimedia Applications

- **Multimedia connections:** USB
- **Playback Formats:** JPEG Still pictures, MP3, Slideshow files (.alb)

### Green Specifications

- **Safety:** Flame retardant housing
- SmartPower<sup>2</sup>
- Eco Designed

## Product highlights

### Lodgenet® HD Built-in

By partnering with Lodgenet, Philips is able to offer you the most convenient and cost effective way to add televisions to a Lodgenet system. Guaranteed to work and certified by Lodgenet, these sets will allow you to sleep as worry free as your guests. No more worrying whether the TV's will arrive before the PPV terminals or cards, and best of all no more costly room visits to install. Because these sets are so easy to install and they work so well with Lodgenet, Lodgenet even offers discounts for those who purchase them (check with your local Lodgenet rep for details).

### Pro:Idiom™ Plus

Pro:Idiom™ was created for the hospitality industry to protect first run movies and other HD premium content from piracy. Philips Pro:Idiom™ Plus televisions offer secure HD content protection not only for PPV hotels, but now also for stand alone properties. (Additional fees may apply for stand alone use) (Pro:Idiom™ is a trademark of the Zenith Corp.)

### VTrack™ forensic watermark

Philips VTrack™ watermarking embeds an invisible forensic watermark in the signal, which can be detected via software to trace pirated content back to the source of recording. Philips VTrack™ is the first solution that protects first run movies and other premium content from optical piracy, helping preserve the early release window that hotels have always enjoyed.

### MPEG-4 for HD

MPEG-4 (Moving Picture Experts Group H.264) compression technology allows more HD content to be delivered than ever before. Satellite providers are already using MPEG-4 to offer the choice of up to 150 national HD channels and 1,500 local broadcast HD and digital channels. Cable, broadcast, and telecommunications providers are expected to also migrate to the format, but with these Philips TVs you are ready today!

### SmartStand

This TV comes with a swivel stand that allows your guests to adjust the TV up to 180 degrees so that they can watch TV from any position in the room. Equipped with built-in security, this stand can be secured to a table or furniture to deter theft.

### Five Star Service

Philips offers unmatched commitment to keeping your guest rooms in working order. Our products are so reliable that we offer a two-year advanced exchange warranty. In the event that something does go wrong, we guarantee to ship a replacement set to you, within 72 hours during the first year.

### SmartPower<sup>2</sup> and ESP

Our second generation power saving technology allows the backlight intensity to be dynamically adjusted by the system to reduce the power consumption by up to 60%, saving substantially on energy costs. In addition, Philips' Energy Savings Programmability (ESP) allows the set to turn itself off when not in use to save even more energy when guests or maids leave televisions on for long periods while the room is vacant.

### RoHS & Flame retardant housing

In addition to being lead-free and RoHS compliant, Philips TVs have a special housing of eco-friendly, non-brominated flame-retardant materials. Independent tests carried out by emergency fire services have shown that whereas TVs can sometimes intensify fires caused by external sources, Philips TVs will not contribute to the fire.



Issue date 2008-09-11  
Owner: Andrew Phang  
Version: 0.3.5

12 NC: 8670 000 42603  
UPC: 6 09585 16060 6

Test leaflet, for internal use only!  
© 2008 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)

\* Five Star Advanced Exchange warranty is valid in the United States only. Local warranties govern sales in other countries.  
\* THIS PRODUCT IS NOT TO BE OFFERED FOR SALE, SOLD, DELIVERED OR USED IN CALIFORNIA